



Main

Range	Masterpact
Product or component type	Ethernet interface module with specific accessories
Condition of use	With specific accessories
Device application	Communication
Range compatibility	Masterpact MTZ2 circuit breaker Masterpact MTZ3 circuit breaker
Device mounting	Embedded

Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP on RJ45 10/100 Mbps
Mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
[Us] rated supply voltage	24 V DC
Supply current	3 A
Power consumption in W	72 W
Product certifications	EAC CE FCC
Standards	IEC 60950 IACS E10 IEC 60947-6-2
Height	2.01 in (51 mm)
Width	2.01 in (51 mm)
Depth	2.07 in (52.5 mm)
Product weight	0.17 lb(US) (0.075 kg)
Web server	Embedded

Environment

IP degree of protection	IP30
Ambient air temperature for operation	-4...158 °F (-20...70 °C)

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1637 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available