


Product data sheet

Specifications



TeSys F - contactor coil - LX0FG - 440 V AC

LX0FG012

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX0FG
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	440 V AC 50/60 Hz
Average Resistance	106.1 Ohm latching 68 °F (20 °C) 8126 Ohm unlatching 68 °F (20 °C)
Product Compatibility	CR1F185
Operating Time	35...40 ms latching 50...100 ms unlatching
Mechanical Durability	1 Mcycles
Maximum Operating Rate	120 cyc/h 104 °F (40 °C)

Complementary

Control Circuit Voltage Limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
--------------------------------	--

Environment

Net Weight	1.23 lb(US) (0.56 kg)
------------	-----------------------

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118109704
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

