
Product data sheet

Specifications





TeSys F - contactor coil - LX0FH - 220...230 V AC/DC

LX0FH008

() Discontinued on: Jan 23, 2021



Main

TeSys
Contactor coil
LX0FH
AC 50400 Hz DC standard
220230 V AC 50400 Hz 220230 V DC
25.77 Ohm latching 68 °F (20 °C) 4090 Ohm unlatching 68 °F (20 °C)
CR1F265
50100 ms unlatching 4550 ms latching
1 Mcycles
120 cyc/h 104 °F (40 °C)

Complementary

Control Circuit Voltage Limits	Latching: 0.851.1 Uc
	Unlatching: 0.851.1 Uc

Environment

Net Weight

1.72 lb(US) (0.78 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	112
Gtin	3389118109636
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9 cm)
Package 1 Width	3.94 in (10 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

 Package 1 Length
 7.32 in (18.6 cm)

 Package 1 Weight
 27.51 oz (780 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information