# **Product data sheet**

Specifications





# Contactor coil, TeSys Deca, LX1D8, 230V AC 50/60Hz for 115 and 150A contactor

LX1D8P7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 98.28 USD

#### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D8
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz
Average Resistance	9895 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	210.72 H
Product Compatibility	LC1D150 LC1D115
Mechanical Durability	8 Mcycles
Maximum Operating Rate	1200 cyc/h 140 °F (60 °C)

## Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.30.5 Uc at 50/60 Hz (at <131 °F (55 °C)) Operational: 0.81.15 Uc at 50/60 Hz (at <131 °F (55 °C))
Inrush Power In Va	280350 VA 60 Hz cos phi 0.9 (at 68 °F (20 °C)) 280350 VA 50 Hz cos phi 0.9 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	218 VA 60 Hz cos phi 0.9 (at 68 °F (20 °C)) 218 VA 50 Hz cos phi 0.9 (at 68 °F (20 °C))
Heat Dissipation	34.5 W 50/60 Hz

#### **Environment**

Ambient Air Temperature For 23...140 °F (-5...60 °C) Operation

## Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
Gtin	03389110868395
Returnability	No
Country Of Origin	CZ

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	4.53 in (11.5 cm)
Package 1 Length	6.69 in (17.0 cm)
Package 1 Weight	10.51 oz (298.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.71 lb(US) (6.673 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov