



TeSys F - contactor coil - LX1FF - 415 V AC 50 Hz

LX1FF415

! Discontinued on: Jul 12, 2021

! Discontinued

Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LX1FF	
Range Compatibility	TeSys TeSys F LC1F contactor	
Product Compatibility	patibility LC1F115 LC1F150	
Control Circuit Type	AC 50 Hz	
[Uc] Control Circuit Voltage	415 V AC 50 Hz	
Inductance Of Closed Circuit	12 H	
Average Resistance	95.1 Ohm 68 °F (20 °C)	
Operating Time	2335 ms closing 515 ms opening	
Mechanical Durability	10 Mcycles	
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)	

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out 0.350.55 Uc 50/60 Hz 131 °F (55 °C)) Operational 0.851.1 Uc 50/60 Hz 131 °F (55 °C))
Inrush Power In Va	550 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	45 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	1216 W 50 Hz

Environment

Ambient Air Temperature For Operation	23131 °F (-555 °C)
Net Weight	0.95 lb(US) (0.43 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS	
Discount Schedule	112	
Gtin	00785901867265	
Returnability	No	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin CZ

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1 1

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information