

Price\*\* : 360.00 USD

LX1FK090 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

### Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX1FK
Range compatibility	TeSys F LC1F contacteur
Product compatibility	LC1F500
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	90 V AC 50/60 Hz
Average resistance	6 Ohm inrush 68 °F (20 °C) 134 Ohm holding 68 °F (20 °C)
Operating time	100...170 ms opening 40...75 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 131 °F (55 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.85...1.1 Uc 50/60 Hz 131 °F (55 °C)) Drop-out 0.3...0.5 Uc 50/60 Hz 131 °F (55 °C))

### Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
---------------------------------------	--------------------------

### Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	03389118108776
Package weight(Lbs)	2.54 lb(US) (1.150 kg)
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------