

Product data sheet

Specifications



TeSys F - contactor coil - LX1FL - 110...120 V AC 40...400 Hz

LX1FL110

Product availability: Stock - Normally stocked in distribution facility

Price*: 477.60 USD

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1FL
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F1250 LC1F630
Control Circuit Type	AC 40...400 Hz
[Uc] Control Circuit Voltage	110...120 V AC 40...400 Hz
Inductance Of Closed Circuit	1.85 H
Average Resistance	6.45 Ohm inrush 68 °F (20 °C) 165 Ohm holding 68 °F (20 °C)
Operating Time	100...200 ms opening 40...80 ms closing
Mechanical Durability	5 Mcycles
Maximum Operating Rate	1200 cyc/h 131 °F (55 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.85...1.1 Uc 40...400 Hz 131 °F (55 °C)) Drop-out 0.25...0.5 Uc 40...400 Hz 131 °F (55 °C))
Inrush Power In Va	1650 VA 40...400 Hz cos phi 0.9 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	22 VA 40...400 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	20 W 40...400 Hz

Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	3.31 lb(US) (1.5 kg)

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0I12
Gtin	3389110082401
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	CZ
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10.0 cm)
Package 1 Width	4.72 in (12.0 cm)
Package 1 Length	8.86 in (22.5 cm)
Package 1 Weight	3.23 lb(US) (1.466 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	20.30 lb(US) (9.21 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information