Product data sheet





TeSys F - contactor coil - LX1FX -220...240 V AC 40...400 Hz

LX1FX220

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 954.00 USD

Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LX1FX	
Range Compatibility	TeSys TeSys F LC1F contactor	
Product Compatibility	LC1F780	
Control Circuit Type	AC 40400 Hz	
[Uc] Control Circuit Voltage	220240 V AC 40400 Hz	
Inductance Of Closed Circuit	0.82 H	
Average Resistance	19.5 Ohm inrush 68 °F (20 °C) 920 Ohm holding 68 °F (20 °C)	
Operating Time 130230 ms opening 4080 ms closing		
Mechanical Durability	5 Mcycles	
Maximum Operating Rate	600 cyc/h 131 °F (55 °C)	

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.851.1 Uc 40400 Hz 131 °F (55 °C)) Drop-out 0.20.4 Uc 40400 Hz 131 °F (55 °C))
Inrush Power In Va	2100 VA 40400 Hz cos phi 0.9 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	50 VA 40400 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	44 W 40400 Hz

Environment

Ambient Air Temperature For Operation	23131 °F (-555 °C)
Net Weight	6.61 lb(US) (3 kg)
Quantity Per Set	Set of 2

Ordering and shipping details

Category	US10l1222341
Discount Schedule	0112
Gtin	3389110083408
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin CZ

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.28 in (18.5 cm)
Package 1 Width	7.28 in (18.5 cm)
Package 1 Length	10.04 in (25.5 cm)
Package 1 Weight	6.36 lb(US) (2.886 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	3
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	21.05 lb(US) (9.55 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information