

# Product data sheet

Specifications



## coil LX4-D - 36 V DC

LX4D6CD

⚠ Discontinued

### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D6
[Uc] Control Circuit Voltage	36 V DC
Average Resistance	51.9 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	4.18 H
Product Compatibility	LC1D80...D95
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

### Complementary

Range Compatibility	TeSys contactor
Coil Technology	Without built-in suppressor module

### Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Net Weight	0.62 lb(US) (0.28 kg)

### Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389110209631
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.