

Product data sheet

Characteristics

LX4D6CD

coil LX4-D - 36 V DC

Price* : 238.00 USD

LX4D6CD has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

| | |
|------------------------------|---------------------------------|
| Range | TeSys |
| Product or component type | Contactor coil |
| Device short name | LX1D6 |
| [Uc] control circuit voltage | 36 V DC |
| Average resistance | 51.9 Ohm at 68 °F (20 °C) |
| Inductance of closed circuit | 4.18 H |
| Product compatibility | LC1D80...D95 |
| Mechanical durability | 10 Mcycles |
| Operating rate | 3600 cyc/h at <= 140 °F (60 °C) |

Complementary

| | |
|---------------------|------------------------------------|
| Range compatibility | TeSys contactor |
| Coil technology | Without built-in suppressor module |

Environment

| | |
|---------------------------------------|--------------------------|
| Ambient air temperature for operation | 23...140 °F (-5...60 °C) |
| Product weight | 0.62 lb(US) (0.28 kg) |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 18401 - WORLD SERVICE PARTS(CTR ACCESS) |
| Discount Schedule | CP10 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.9100000000000003 |
| Returnability | N |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|