


LX4D8UD

TeSys D - contactor coil - LX4D8 - 250 V DC
standard for 115 & 150 A contactor

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 81.90 USD



Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4D8
Control circuit type	DC standard
[Uc] control circuit voltage	250 V DC
Average resistance	18022 Ohm at 68 °F (20 °C)
Inductance of closed circuit	345.4 H
Product compatibility	LC1D150 LC1D115
Mechanical durability	8 Mcycles
Operating rate	1200 cyc/h at <= 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.15...0.4 Uc at 131 °F (55 °C) drop-out 0.75...1.2 Uc at 131 °F (55 °C) operational
Time constant	25 ms
Inrush power in W	270...365 W at 68 °F (20 °C)
Hold-in power consumption in W	2.4...5.1 W at 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Product weight	0.66 lb(US) (0.3 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
----------	---------------------------------

Discount Schedule	I12
GTIN	003389110115604
Nbr. of units in pkg.	1
Package weight(Lbs)	0.6600000000000003
Returnability	N
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0847 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------