

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 725.00 USD



### Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4F8
Range compatibility	TeSys F LC1F contacteur
Product compatibility	LC1F800
Control circuit type	DC low consumption
[Uc] control circuit voltage	110...120 V DC
Operating time	40...50 ms opening 60...80 ms closing
Mechanical durability	5 Mcycles
Operating rate	<= 600 cyc/h at <= 55 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	1900 W at 68 °F (20 °C)
Hold-in power consumption in W	12 W at 68 °F (20 °C)

### Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	3.64 lb(US) (1.65 kg)

### Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901526797

Nbr. of units in pkg.	1
Package weight(Lbs)	3.77
Returnability	N
Country of origin	CZ

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0830 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------