

Price** : 580.00 USD

LX4FJ045 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FJ
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F400
Control circuit type	DC low consumption
[Uc] control circuit voltage	45 V DC
Average resistance	1.98 Ohm inrush 68 °F (20 °C) 526.1 Ohm holding 68 °F (20 °C)
Operating time	45...60 ms opening 50...60 ms closing

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.2...0.35 Uc 131 °F (55 °C) Operational 0.85...1.1 Uc 131 °F (55 °C)

Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
---------------------------------------	--------------------------

Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	03389118114166
Package weight(Lbs)	2.14 lb(US) (0.970 kg)
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------