

Price** : 730.00 USD

LX4FK090 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

| | |
|------------------------------|---|
| Range | TeSys |
| Product or component type | Contacteur coil |
| Device short name | LX4FK |
| Range compatibility | TeSys F LC1F contacteur |
| Product compatibility | LC1F500 |
| Control circuit type | DC low consumption |
| [Uc] control circuit voltage | 90 V DC |
| Average resistance | 1917 Ohm holding 68 °F (20 °C) 7.47 Ohm inrush 68 °F (20 °C) |
| Operating time | 45...60 ms opening 50...60 ms closing |

Complementary

| | |
|--------------------------------|---|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | Drop-out 0.2...0.35 Uc 131 °F (55 °C) Operational 0.85...1.1 Uc 131 °F (55 °C) |

Environment

| | |
|---------------------------------------|--------------------------|
| Ambient air temperature for operation | 23...131 °F (-5...55 °C) |
|---------------------------------------|--------------------------|

Ordering and shipping details

| | |
|---------------------|---------------------------------------|
| Category | 18401-WORLD SERVICE PARTS(CTR ACCESS) |
| Discount Schedule | CP10 |
| GTIN | 03389118113947 |
| Package weight(Lbs) | 2.38 lb(US) (1.080 kg) |
| Returnability | No |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|