

LX9FK915

specific contactor coil - TeSys F - 32..34 V DC - low consumption

Price** : 360.00 USD

LX9FK915 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FK
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F500
Control circuit type	DC low consumption
[Uc] control circuit voltage	32...34 V DC
Operating time	60 ms opening 50 ms closing
Mechanical durability	10 Mcycles
Operating rate	<= 3600 cyc/h at <= 70 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in VA	550 VA at 68 °F (20 °C)
Hold-in power consumption in VA	31 VA at 68 °F (20 °C)
Heat dissipation	15...18.3 W

Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	2.38 lb(US) (1.08 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	2.3799999999999999
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
