## **Product data sheet**

Specification





# Multi9 - undervoltage release - MN - 24 V AC - 24 V DC

M9A27108

Product availability: Stock - Normally stocked in distribution facility

Price\*: 201.00 USD

#### Main

Range Of Product	Multi9
Product Or Component Type	Undervoltage release
Device Short Name	MN
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz 24 V DC
Control Type	Standard
9 Mm Pitches	2

### Complementary

Range Compatibility	Multi 9 Multi9 C60 C60BP Multi 9 Multi9 C60 C60BPR Multi 9 Multi9 C60 C60SP Multi 9 Multi9 GFP GFP Multi 9 Multi9 C60H-DC C60H-DC
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top YES
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Net Weight	0.15 lb(US) (0.066 kg)
Connections - Terminals	Clamp terminal bottom) - 1 0.00 in² (2.5 mm²) AWG 14) - rigid Clamp terminal bottom) - 2 0.00 in² (1.5 mm²) AWG 16) - rigid
Wire Stripping Length	0.35 in (9 mm) for bottom connection
Tightening Torque	8.85 lbf.in (1 N.m) bottom

#### **Environment**

Standards	EN/IEC 60947-1		
	EN 60947-2		
	UL 489		
	UL 1077		
	C22.2 No. 5		
	GB/T 14048.5		
Product Certifications	PCT		
	UR		
	UL		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Pollution Degree	3
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

## Ordering and shipping details

Category	US10DE200948
Discount Schedule	0DE2
Gtin	3606480639173
Returnability	Yes
Country Of Origin	BE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.14 in (2.900 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	3.70 in (9.400 cm)
Package 1 Weight	2.57 oz (73.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	3.43 in (8.700 cm)
Package 2 Width	3.94 in (10.000 cm)
Package 2 Length	10.43 in (26.500 cm)
Package 2 Weight	23.00 oz (652.000 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	32
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	6.81 lb(US) (3.088 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information