

MGF36800

PowerPact M-FRAME MOULDED CASE CIRCUIT BREAKER 600V 800A 3P

Product availability : Stock - Normally stocked in distribution facility



Price* : 9,927.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact M
Breaking capacity code	G

Complementary

Current sensor rating range	800 A
Line Rated Current	800 A
System Voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Continuous current rating	80 %
Electrical connection	Busbar connection load Busbar connection line
Tightening torque	50 N.m for 95...240 mm ² (AWG 3/0...500 kcmil)

Environment

Product certifications	UL listed CSA
------------------------	------------------

Ordering and shipping details

Category	01205 - MG, MJ UNIT MOUNT BREAKER
Discount Schedule	DE2
GTIN	00785901477020

Nbr. of units in pkg.	1
Package weight(Lbs)	28
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------