

MGL36300

PowerPact M Molded CASE CIRCUIT BREAKER

600V 300A 3P

Product availability : Stock - Normally stocked in distribution facility



Price** : 7,560.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact M
Breaking capacity code	G
Trip unit technology	Electronic, basic, ET 1.0, LI

Complementary

Current sensor rating range	300 A
Line Rated Current	300 A
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Continuous current rating	80 %
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 3/0...500 kcmil aluminium/copper)3
Terminal identifier	AL800M23K
Tightening torque	442.54 lbf.in (50 N.m) 0.15...0.37 in ² (95...240 mm ²) AWG 3/0...500 kcmil)

Environment

Product certifications	IEC CSA UL listed
------------------------	-------------------------

Ordering and shipping details

Category	01205 - MG, MJ UNIT MOUNT BREAKER
Discount Schedule	DE2
GTIN	00785901507635
Package weight(Lbs)	13.15 kg (29 lb(US))
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------