





# Enclosure box, NQ and NF panelboards, NEMA 1, 20in W x 50in H x 5.75in D

Product availability: Stock - Normally stocked in distribution facility

Price\*: 113.00 USD

### Main

Product Enclosure

# Complementary

Material	Steel
Height	50 in (1270.00 mm)
Width	20 in (508.00 mm)
Depth	5.75 in (146.05 mm)

## **Environment**

Enclosure Rating	NEMA 1
Product Certifications	cULus

# Ordering and shipping details

Category	US1PE1A07969		
Discount Schedule	PE1A		
Gtin	785901378914		
Returnability	Yes		
Country Of Origin	US		

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	0.63 in (1.6 cm)		
Package 1 Width	2.04 in (5.182 cm)		
Package 1 Length	5.00 in (12.7 cm)		
Package 1 Weight	31.07 lb(US) (14.093 kg)		

# **Contractual warranty**

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance


<b>②</b>	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

### **Dimensions Drawings**

### **Approximate Dimensions**



KNOCKOUTS					
CVALDOI	CONDUIT SIZE		KNOCKOUT DIA		
SYMBOL	IN	MM	IN	MM	
Α	.50	13	.88	22	
В	.75	19	1.12	28	
D	1.25	32	1.75	44	
E	1.50	38	2.00	51	
F	2.00	51	2.50	64	
G	2.50	64	3.00	76	
Н	3.00	76	3.62	92	
ı	3.50	89	4.12	105	



CATALOG	L		S		М	
REF NO	IN	ММ	IN	ММ	IN	ММ
MH26	26.00	660	21.00	533	20.00	508
MH32	32.00	813	27.00	686	26.00	660
MH38	38.00	965	33.00	838	32.00	813
MH44	44.00	1118	39.00	991	38.00	965
MH50	50.00	1270	45.00	1143	44.00	1118
MH56	56.00	1422	51.00	1295	50.00	1270
MH62	62.00	1575	57.00	1448	56.00	1422
MH68	68.00	1727	63.00	1600	62.00	1575
MH74	74.00	1880	69.00	1753	68.00	1727
MH80	80.00	2032	75.00	1905	74.00	1880
MH86	86.00	2184	81.00	2057	80.00	2032
MH92	92.00	2337	87.00	2210	86.00	2184