

# Product data sheet

## Characteristics

# MPZ15S40F

## MINI PWR-ZONE DRY 1P 15KVA

### 480V-120/240V

Product availability : Stock - Normally stocked in distribution facility



Price\* : 6,410.00 USD



### Main

Product	Sealed Transformer
Certifications	UL listed
Type	Mini Power-Zone
Enclosure Code	B
Insulation Temperature	365 °F (185 °C)
Phase	1 phase
Primary Voltage	480 V
Secondary Voltage	120/240 V
Full Capacity Taps	2 5 % FCBN
Power Rating	15 kVA
Temperature Rise	115 °C
Winding Material	Copper
Interrupt Rating	18 kA
Circuit Breaker Type	Primary main breaker Secondary main breaker Feeder breaker
Interior Type	QO Load Center interior
Number of Spaces Available	24
Number of Circuits	24
Enclosure Type	NEMA 3R hot-rolled steel

### Ordering and shipping details

Category	16275 - MPZ PLUG ON BRANCH CB
Discount Schedule	PE2
GTIN	00785901838975
Nbr. of units in pkg.	1

Package weight(Lbs)	365
Returnability	Y
Country of origin	US

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel (Metallic), which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------