

Product data sheet

Characteristics

NF442L2

NF Panelboard, interior, main lug, 250 A, 3 PH, 4 wire, 42 CCT, Al

Product availability : Stock - Normally stocked in distribution facility



Price** : 2,418.00 USD



Main

Load center type	Main lugs
Branch Circuit Breaker Type	EDB/EDG/EDJ
Connections - terminals	Lug line AWG 6...350 kcmil aluminium Lug neutral AWG 6...350 kcmil aluminium
Busbar Material	Aluminium

Complementary

Number of spaces	42
Enclosure Nominal Height	56 in 44 in
Enclosure Nominal Width	20 in
Enclosure Nominal Width	5.75 inFor NEMA 1 enclosure 6.5 inFor NEMA 3R/5/12 enclosure
Line Rated Current	250 A
Wiring configuration	4-wire
Phase	3 phases
System Voltage	480Y/277 V AC

Environment

Standards	CSA C22.2 UL 67
-----------	--------------------

Ordering and shipping details

Category	08350 - NF MLO INTERIOR RTA
Discount Schedule	PE1A
GTIN	00785901871569

Nbr. of units in pkg.	1
Package weight(Lbs)	21.650000000000002
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1419 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds which is known to the State of California to cause cancer and
----- Substance 2	Bisphenol A (BPA) which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------