





Panelboard interior, NF, main lugs, 400A, Al bus, 42 pole spaces, 3 phase, 4 wire, 600Y/347VAC max

NF442L4

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,673.00 USD

Main

Panelboard Type	Main lugs
Branch Circuit Breaker Type	EDB/EDG/EDJ
Busbar Material	Aluminium

Complementary

Number Of Spaces	42
Enclosure Nominal Height	56 in (1422.40 mm) 68 in (1727.20 mm)
Enclosure Nominal Width	20 in (508.00 mm)
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12
Line Rated Current	400 A
[lu] Rated Interrupted Current	65 kA
Wiring Configuration	4-wire
Number Of Phases	3 phase
Voltage Rating	600Y/347 V AC
Connections - Terminals	Lug line AWG 1/0750 kcmil aluminium Lug neutral AWG 1/0750 kcmil aluminium
Tightening Torque	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in² (53.48177.3 mm²) (AWG 1/0350 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil)
Height	52 in (1320.80 mm)
Width	10.44 in (265.18 mm)

Environment

Standards	UL 67
	CSA C22.2

Ordering and shipping details

Category	US1PE1A08350
Discount Schedule	PE1A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901871606	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.30 in (16.0 cm)
Package 1 Width	14.21 in (36.1 cm)
Package 1 Length	55.98 in (142.2 cm)
Package 1 Weight	26.12 lb(US) (11.85 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	9
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	60.00 in (152.4 cm)
Package 2 Weight	441.40 lb(US) (200.214 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov