





Panelboard interior, NQ, main lugs, 100A, Al bus, 18 pole spaces, 3 phase, 4 wire, 240VAC, 48VDC

NQ418L1

Product availability: Stock - Normally stocked in distribution facility

Price*: 876.00 USD

Main

Panelboard Type	Main lugs
Product Or Component Type	Interiors
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Aluminium

Complementary

Number Of Spaces	18
Enclosure Nominal Height	26 in (660.40 mm)
Enclosure Nominal Width	20 in (508.00 mm)
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12
Line Rated Current	100 A
[lu] Rated Interrupted Current	10 kA 22 kA 65 kA
Number Of Phases	3 phase 4 wires
Voltage Rating	240 V AC 48 V DC
Connections - Terminals	Lug line AWG 6AWG 2/0 aluminium Lug neutral AWG 6AWG 2/0 aluminium
Tightening Torque	40.0150.01 lbf.in (4.525.65 N.m) 0.020.10 in² (13.3067.43 mm²) (AWG 6AWG 2/0) 100.01 lbf.in (11.3 N.m) 0.020.10 in² (13.3067.43 mm²) (AWG 6AWG 2/0) 274.99 lbf.in (31.07 N.m) 0.020.27 in² (13.30177.3 mm²) (AWG 6350 kcmil) 274.99 lbf.in (31.07 N.m) 0.020.20 in² (13.30126.7 mm²) (AWG 6250 kcmil) 274.99 lbf.in (31.07 N.m) 0.170.24 in² (107.2152 mm²) (AWG 4300 kcmil)
Height	27 in (685.80 mm)
Width	10.44 in (265.18 mm)

Environment

Standards	UL
	CSA

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US1PE1A09151
Discount Schedule	PE1A
Gtin	785901502128
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.30 in (16.002 cm)
Package 1 Width	14.00 in (35.56 cm)
Package 1 Length	26.00 in (66.04 cm)
Package 1 Weight	11.94 lb(US) (5.416 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
Ø	Mercury Free	
9	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov