

# Product data sheet

## Characteristics

# NQ42L2

NQ Panelboard, interior, main lug, 225 A, 1 PH, 3 wire, 42 CCT, AI

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 1,340.00 USD



### Main

Load center type	Main lugs
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Aluminium

### Complementary

Number of spaces	42
Enclosure Nominal Height	38 in
Enclosure Nominal Width	20 in
Enclosure Nominal Width	5.75 in For NEMA 1 enclosure 6.5 in For NEMA 3R/5/12 enclosure
Line Rated Current	225 A
Wiring configuration	3-wire
Phase	1 phase
System Voltage	240 V AC 48 V DC

### Environment

Standards	CSA UL
-----------	-----------

### Ordering and shipping details

Category	09151 - NQ RTA PANELBOARDS
Discount Schedule	PE1A
GTIN	00785901502180
Nbr. of units in pkg.	1

Package weight(Lbs)	18.100000000000001
Returnability	Y
Country of origin	MX

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1419 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds which is known to the State of California to cause cancer and
----- Substance 2	Bisphenol A (BPA) which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------