

Product data sheet

Characteristics

NQ454L2

NQ Panelboard, interior, main lug, 225 A, 3 PH, 4 wire, 54 CCT, AI

Product availability : Stock - Normally stocked in distribution facility



Price** : 1,898.00 USD



Main

Load center type	Main lugs
Branch Circuit Breaker Type	QOB QOB-VH QHB
Connections - terminals	Lug line AWG 6...350 kcmil aluminium Lug neutral AWG 6...350 kcmil aluminium
Busbar Material	Aluminium

Complementary

Number of spaces	54
Enclosure Nominal Height	38 in
Enclosure Nominal Width	20 in
Enclosure Nominal Width	5.75 in For NEMA 1 enclosure 6.5 in For NEMA 3R/5/12 enclosure
Line Rated Current	225 A
Wiring configuration	4-wire
Phase	3 phases
System Voltage	240 V AC 48 V DC
Tightening torque	4.52...5.65 N.m 13.3...67.43 mm ² (AWG 6...AWG 2/0) 100 lbf.in (11.3 N.m) 13.3...67.43 mm ² (AWG 6...AWG 2/0) 31.07 N.m 13.3...177.3 mm ² (AWG 6...350 kcmil) 31.07 N.m 13.3...126.7 mm ² (AWG 6...250 kcmil) 31.07 N.m 107.2...152 mm ² (AWG 4...300 kcmil)

Environment

Standards	UL CSA
-----------	-----------

Ordering and shipping details

Category	09151 - NQ RTA PANELBOARDS
Discount Schedule	PE1A
GTIN	00785901830665
Nbr. of units in pkg.	1
Package weight(Lbs)	19
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1419 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds which is known to the State of California to cause cancer and
----- Substance 2	Bisphenol A (BPA) which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------