





Panelboard interior, NQ, main lugs, 225A, Cu bus, 72 pole spaces, 1 phase, 3 wire, 240VAC, 48VDC

NQ72L2C

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,430.00 USD

Main

Panelboard Type	Main lugs
Product Or Component Type	Interiors
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Copper

Complementary

Number Of Spaces	72
Enclosure Nominal Height	44 in (1117.60 mm)
Enclosure Nominal Width	20 in (508.00 mm)
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12
Line Rated Current	225 A
[lu] Rated Interrupted Current	10 kA 22 kA 65 kA
Wiring Configuration	3-wire
Number Of Phases	1 phase
Voltage Rating	240 V AC 48 V DC
Tightening Torque	40.0150.01 lbf.in (4.525.65 N.m) 0.020.10 in² (13.3067.43 mm²) (AWG 6AWG 2/0) 100.01 lbf.in (11.3 N.m) 0.020.10 in² (13.3067.43 mm²) (AWG 6AWG 2/0) 274.99 lbf.in (31.07 N.m) 0.020.27 in² (13.30177.3 mm²) (AWG 6350 kcmil) 274.99 lbf.in (31.07 N.m) 0.020.20 in² (13.30126.7 mm²) (AWG 6250 kcmil) 274.99 lbf.in (31.07 N.m) 0.170.24 in² (107.2152 mm²) (AWG 4300 kcmil)
Height	39 in (990.60 mm)
Width	10.44 in (265.18 mm)

Environment

Standards	UL	
	CSA	

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US1PE1A09151
Discount Schedule	PE1A
Gtin	785901856320
Returnability	Yes
Country Of Origin	MX

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.42 in (16.3 cm)
Package 1 Width	14.02 in (35.6 cm)
Package 1 Length	44.02 in (111.8 cm)
Package 1 Weight	24.87 lb(US) (11.28 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	6
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	156.86 lb(US) (71.151 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov