Product data sheet

Specifications





Brush-type cable entry gasket, PanelSeT SFN, Spacial SF, for electrical enclosure W1200mm, set of 2

NSYBCE12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 54.90 USD

Main

Range	Spacial
Product Or Component Type	Brush gasket
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial SF suitable enclosure
Device Composition	2 gasket
Quantity Per Set	Set of 1

Complementary

Mounting Support	Cable gland plate
Cable Entry	1 or 2 entries
Fixing Mode	Clipped
Height	1.57 in (40 mm)
Width	Nominal 47.24 in (1200 mm) Real 19.88 in (505 mm)
Depth	0.98 in (25 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485130019
Returnability	No
Country Of Origin	FR

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	29.13 in (74.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Weight	20.04 oz (568.0 g)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	240
Package 2 Height	47.24 in (120.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	309.81 lb(US) (140.528 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations