

Product data sheet

Characteristics

NSYBCE4

Spacial SF brush flexible cable entry gaskets - 25 mm - 400 mm enclosure

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 8.58 USD



Main

Range	Spacial
Product or component type	Brush gasket
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial SF suitable enclosure
Device composition	2 gasket
Quantity per set	Set of 1

Complementary

Mounting support	Cable gland plate
Cable entry	1 or 2 entries
Fixing mode	Clipped
Height	1.57 in (40 mm)
Width	Nominal: 15.75 in (400 mm) Real : 305 mm
Depth	0.98 in (25 mm)

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	003606485130040
Nbr. of units in pkg.	1
Package weight(Lbs)	299.19999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------