Product data sheet

Specification





Brush-type cable entry gasket, PanelSeT SFN, Spacial SF, for electrical enclosure W800mm, set of 2

NSYBCE8

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 33.84 USD

Main

Range	Spacial
Product Or Component Type	Brush gasket
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial SF suitable enclosure
Device Composition	2 gasket
Quantity Per Set	Set of 1

Complementary

Mounting Support	Cable gland plate	
Cable Entry	1 or 2 entries	
Fixing Mode	Clipped	
Height	2.76 in (70 mm)	
Width	Nominal 31.50 in (800 mm) Real 28.94 in (735 mm)	
Depth	0.98 in (25 mm)	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485130064
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	29.13 in (74.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight	15.03 oz (426.0 g)	
Unit Type Of Package 2	P12	
Number Of Units In Package 2	120	
Package 2 Height	41.34 in (105.0 cm)	
Package 2 Width	31.50 in (80.0 cm)	
Package 2 Length	47.24 in (120.0 cm)	
Package 2 Weight	203.27 lb(US) (92.2 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations