



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Electronical thermostat
Temperature setting range	-40...176 °F (-40...80 °C)
Display type	OLED screen
Information displayed	Temperature in °C Temperature in °F

Complementary

Input voltage	90...140 V AC
Sensor type	Optional NTC external sensor
Maximum switching capacity	4 A 120 V AC
Electrical connection	10 terminals 2.5 mm ²
Mounting mode	Clipped By screws
Height	External: 3.35 in (85 mm)
Width	External: 2.2 in (56 mm)
Depth	External: 1.73 in (44 mm)
Mounting location	On mounting plate 35 mm DIN rail Cross rails Spacial upright
Ambient air temperature for operation	-40...176 °F (-40...80 °C)
Hysteresis	2 K programmed value
Number of outputs	2 output(s) ventilation/heating function
Material	PC
Color	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UR

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901860570
Nbr. of units in pkg.	1
Package weight(Lbs)	0.29999999999999999
Returnability	Y
Country of origin	ES

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------