Product data sheet

Specifications





Climasys CC - Electronical thermostat 95...135V - range of temperature -40...80°C

NSYCCOTH120VID

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 229.96 USD

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Electronical thermostat
Temperature Setting Range	-40176 °F (-4080 °C)
Display Type	OLED screen
Information Displayed	Temperature in °F Temperature in °C

Complementary

-	
Input Voltage	90140 V AC
Sensor Type	Optional NTC external sensor
Maximum Switching Capacity	4 A 120 V AC
Electrical Connection	10 terminals 2.5 mm²
Mounting Mode	By screws Clipped
Height	External 3.35 in (85 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Mounting Location	Spacial upright 35 mm DIN rail Cross rails On mounting plate
Ambient Air Temperature For Operation	-40176 °F (-4080 °C)
Hysteresis	2 K programmed value
Number Of Outputs	2 ventilation/heating function
Material	PC
Color	Light gray
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

Ordering and shipping details

Category US10ES180036

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0ES1
Gtin	3606480152610
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	1.97 in (5.0 cm)
Package 1 Weight	2.47 oz (70.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations