# **Product data sheet**

Specification





ClimaSys CC - thermostat 250V - range of temperature +5...60°C - 1 NO/NC - °C

NSYCCOTHI

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 48.00 USD

#### Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Thermostat
Temperature Setting Range	41140 °F (560 °C)
Information Displayed	Temperature in °C

### Complementary

Input Voltage	250 V
Sensor Type	Bimetal
Contacts Type And Composition	1 NO/NC
Contact Resistance	10 mOhm
Service Life In Cycles	100000 cycles
Maximum Switching Capacity	4 A 250 V AC inductive 0.6 30 W DC 10 A 250 V AC inductive
Electrical Connection	4 terminals 2.5 mm <sup>2</sup>
Mounting Mode	Clipped
Height	External 2.68 in (68 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Net Weight	3.53 oz (100 g)
Mounting Location	Cross rails On mounting plate 35 mm DIN rail Spacial upright
Ambient Air Temperature For Operation	-4176 °F (-2080 °C)
Ip Degree Of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number Of Outputs	1 heating function 1 ventilation function
Material	PC
Color	Light gray

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480152559
Returnability	No
Country Of Origin	CN

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	2.76 in (7 cm)
Package 1 Weight	2.82 oz (80 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	75
Package 2 Height	10.24 in (26 cm)
Package 2 Width	16.34 in (41.5 cm)
Package 2 Length	12.80 in (32.5 cm)
Package 2 Weight	16.38 lb(US) (7.428 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	3000
Package 3 Height	77.95 in (198 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	685.64 lb(US) (311 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations