Product data sheet

Specification





ClimaSys CC - simple thermostat 250V - range of temperature 0... 60°C - NO - °F

NSYCCOTHOF

Product availability: Stock - Normally stocked in distribution facility

Price*: 47.40 USD

Main

| Range | ClimaSys |
|---------------------------|-------------------|
| Product Name | ClimaSys CC |
| Product Or Component Type | Simple thermostat |
| Temperature Setting Range | 32140 °F (060 °C) |
| Information Displayed | Temperature in °F |

Complementary

| Input Voltage | 250 V |
|---------------------------------------|--|
| Sensor Type | Bimetal |
| Contacts Type And Composition | NO |
| Contact Resistance | 10 mOhm |
| Service Life In Cycles | 100000 cycles |
| Maximum Switching Capacity | 2 A 120250 V AC inductive 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC |
| Electrical Connection | 4 terminals 2.5 mm ² |
| Mounting Mode | Clipped |
| Height | External 2.68 in (68 mm) |
| Width | External 1.30 in (33 mm) |
| Depth | External 1.73 in (44 mm) |
| Net Weight | 1.41 oz (40 g) |
| Mounting Location | Spacial upright 35 mm DIN rail On mounting plate Cross rails |
| Ambient Air Temperature For Operation | -4176 °F (-2080 °C) |
| Ip Degree Of Protection | IP20 |
| Hysteresis | 7 K +/- 0.4K |
| Hysteresis | 7 % |
| Number Of Outputs | 1 ventilation function |
| Material | PC |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Color | Light gray |
|------------------------|---|
| Flame Retardance | Self-extinguishing conforming to UL94 (material V0) |
| Product Certifications | |

Ordering and shipping details

| Category | US10ES180036 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480152535 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.36 in (6 cm) |
| Package 1 Width | 1.57 in (4 cm) |
| Package 1 Length | 1.38 in (3.5 cm) |
| Package 1 Weight | 2.12 oz (60 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |