Product data sheet

Specification





Spacial CRN plain door w/o mount.plate. H1000xW800xD250 IP66 IK10 RAL7035..

NSYCRN108250

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 367.13 USD

Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	39.37 in (1000 mm)
Enclosure Nominal Width	31.50 in (800 mm)
Enclosure Nominal Depth	9.84 in (250 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 2 cable gland plate bottom
Door Type	Solid
Mounting Plate Description	Without mounting plate

Complementary

Body Type	Back welded with double profile forming a protected sealed area Sides made from a single folded section	
Number Of Doors	Front face 1	
Door Opening Side	Reversible 120 °)	
Lock Type	3 mm double-bar lock	
Type Of Gland Plate	Standard	
Accessibility For Operation	Front	
Removable Parts	Door by hinges Cable gland plate by screws	
Material	Body steel	
Surface Finish	epoxy-polyester powder	
Color	Gray RAL 7035)	
Standards	IEC 62208	
Product Certifications	UL cUL DNV-GL	
Net Weight	72.75 lb(US) (33 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	03606480212710
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.63 in (27.0 cm)
Package 1 Width	31.89 in (81.0 cm)
Package 1 Length	39.96 in (101.5 cm)
Package 1 Weight	62.76 lb(US) (28.466 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	8
Package 2 Height	68.90 in (175.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	530.71 lb(US) (240.728 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations