

# Product data sheet

## Characteristics

# NSYCRN108300P

Spacial CRN plain door with mount.plate.  
H1000xW800xD300 IP66 IK10 RAL7035..

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 546.28 USD



### Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	39.37 in (1000 mm)
Enclosure nominal width	31.5 in (800 mm)
Enclosure nominal depth	11.81 in (300 mm)
Installation accessory type	Wall-mounting
Device composition	Body 1 Mounting plate 1 Door with lock 1 Cable gland plate 2 bottom
Door type	Plain
Mounting plate description	Plain

### Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Galvanised steel mounting plate Steel enclosure

Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure:
Standards	IEC 62208
Product certifications	CUL UL
Product weight	108.03 lb(US) (49 kg)

## Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480212673
Nbr. of units in pkg.	1
Package weight(Lbs)	107.69
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------