Product data sheet

Specifications





Spacial CRN plain door with mount.plate. H250xW200xD150 IP66 IK10 RAL7035..

NSYCRN252150P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 106.12 USD

Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	9.84 in (250 mm)
Enclosure Nominal Width	7.87 in (200 mm)
Enclosure Nominal Depth	5.91 in (150 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door with lock 1 mounting plate
Door Type	Solid
Mounting Plate Description	Plain

Complementary

Body Type	Back welded with double profile forming a protected sealed area Sides made from a single folded section
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface Finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL cUL DNV-GL

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight 7.22 lb(US) (3.274 kg)

Environment

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480212628
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.69 in (17.0 cm)
Package 1 Width	8.66 in (22.0 cm)
Package 1 Length	10.63 in (27.0 cm)
Package 1 Weight	7.22 lb(US) (3.274 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	140
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	68.90 in (175 cm)
Package 2 Weight	1038.38 lb(US) (471 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations