# **Product data sheet**

Specifications





# Spacial CRN tspt door w/o mount.plate. H600xW600xD200 IP66 IK08 RAL7035..

NSYCRN66200T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 461.98 USD

### Main

| Range                       | Spacial   |
|-----------------------------|---|
| Product Name                | Spacial CRN                                       |
| Application                 | Multi-purpose                                     |
| Category                    | Compact enclosure                                 |
| Enclosure Nominal Height    | 23.62 in (600 mm)                                 |
| Enclosure Nominal Width     | 23.62 in (600 mm)                                 |
| Enclosure Nominal Depth     | 7.87 in (200 mm)                                  |
| Installation Accessory Type | Wall-mounting                                     |
| Device Composition          | 1 body<br>1 cable gland plate<br>1 door<br>1 lock |
| Door Type                   | Glass   |
| Mounting Plate Description  | Without mounting plate                            |

## Complementary

| Body Type                   | Sides made from a single folded section  Back welded with double profile forming a protected sealed area |
|-----------------------------|--|
| Number Of Doors             | Front face 1   |
| Door Opening Side           | Reversible 120 °)  |
| Lock Type                   | 3 mm double-bar lock   |
| Type Of Gland Plate         | Standard   |
| Accessibility For Operation | Front  |
| Removable Parts             | Door by hinges<br>Cable gland plate by screws  |
| Material                    | Body steel<br>Door steel and security glass  |
| Surface Finish              | epoxy-polyester powder   |
| Color                       | Gray RAL 7035)   |
| Standards                   | IEC 62208  |
| Product Certifications      | UL<br>cUL<br>DNV-GL  |
| Net Weight                  | 28.99 lb(US) (13.148 kg)   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

| Ip Degree Of Protection | IP66 IEC 60529 |
|-------------------------|----------------|
| Ik Degree Of Protection | IK08 IEC 62262 |

## Ordering and shipping details

| Category          | US10ES180034  |
|-------------------|---------------|
| Discount Schedule | 0ES1          |
| Gtin              | 3606480212000 |
| Returnability     | No            |
| Country Of Origin | ES            |

## **Packing Units**

| Unit Type Of Package 1       | PCE                      |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1                        |
| Package 1 Height             | 24.41 in (62.0 cm)       |
| Package 1 Width              | 24.41 in (62.0 cm)       |
| Package 1 Length             | 8.66 in (22.0 cm)        |
| Package 1 Weight             | 28.99 lb(US) (13.148 kg) |
| Unit Type Of Package 2       | PAM                      |
| Number Of Units In Package 2 | 18                       |
| Package 2 Height             | 47.24 in (120 cm)        |
| Package 2 Width              | 39.37 in (100 cm)        |
| Package 2 Length             | 77.95 in (198 cm)        |
| Package 2 Weight             | 548.95 lb(US) (249 kg)   |

## **Contractual warranty**

Warranty 18 months

Apr 19, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration  |
|--------------------------|--|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile  |
| Circularity Profile      | No need of specific recycling operations   |