

# Product data sheet

## Characteristics

# NSYCRN75200

Spacial CRN plain door w/o mount.plate.  
H700xW500xD200 IP66 IK10 RAL7035..

Product availability : Stock - Normally stocked in distribution facility



Price\* : 183.24 USD



### Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	27.56 in (700 mm)
Enclosure nominal width	19.69 in (500 mm)
Enclosure nominal depth	7.87 in (200 mm)
Installation accessory type	Wall-mounting
Device composition	Lock 1 Door 1 Body 1 Cable gland plate 1
Door type	Plain
Mounting plate description	Without mounting plate

### Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Steel body
Surface finish	Epoxy-polyester powder

Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	CUL UL
Product weight	14.222 kg

### Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

### Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901896180
Nbr. of units in pkg.	1
Package weight(Lbs)	30.600000000000001
Returnability	Y
Country of origin	ES

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------