# **Product data sheet**

Specification





# Spacial CRN plain door w/o mount.plate. H800xW600xD200 IP66 IK10 RAL7035..

NSYCRN86200

Product availability: Stock - Normally stocked in distribution

Price\*: 227.88 USD

### Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	31.50 in (800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
<b>Enclosure Nominal Depth</b>	7.87 in (200 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door 1 lock
Door Type	Solid
Mounting Plate Description	Without mounting plate

## Complementary

Body Type	Back welded with double profile forming a protected sealed area Sides made from a single folded section	
Number Of Doors	Front face 1	
Door Opening Side	Reversible 120 °)	_
Lock Type	3 mm double-bar lock	_
Type Of Gland Plate	Standard	
Accessibility For Operation	Front	
Removable Parts	Door by hinges Cable gland plate by screws	
Material	Body steel	_
Surface Finish	epoxy-polyester powder	
Color	Gray RAL 7035)	
Standards	IEC 62208	
Product Certifications	cUL UL DNV-GL	
Net Weight	39.99 lb(US) (18.138 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480211850
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.46 in (21.500 cm)
Package 1 Width	24.21 in (61.500 cm)
Package 1 Length	32.09 in (81.500 cm)
Package 1 Weight	40.44 lb(US) (18.344 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	15
Package 2 Height	77.56 in (197.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	635.28 lb(US) (288.160 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations