# Product data sheet

Specifications





# Spacial CRN tspt door w/o mount.plate. H800xW600xD200 IP66 IK08 RAL7035..

NSYCRN86200T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 473.46 USD

#### Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	31.50 in (800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door 1 lock
Door Type	Glass
Mounting Plate Description	Without mounting plate

### Complementary

Body Type	Sides made from a single folded section  Back welded with double profile forming a protected sealed area
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body steel Door steel and security glass
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL DNV-GL
Net Weight	38.38 lb(US) (17.41 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK08 IEC 62262

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480211836
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.28 in (82.0 cm)
Package 1 Width	24.41 in (62.0 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	38.38 lb(US) (17.41 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	12
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	77.17 in (196 cm)
Package 2 Weight	487.22 lb(US) (221 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations