Product data sheet

Specifications

≺Green Premium"



() Discontinued

Spacial CRNG tspt door w/o mount.plate. H1000xW1000xD300 IP66 IK08 RAL7035

NSYCRNG1010300T

Discontinued on: Jun 7, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Μ	ai	n
	~	•••

mann	
Range	Spacial
Product Name	Spacial CRNG
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	39.37 in (1000 mm)
Enclosure Nominal Width	39.37 in (1000 mm)
Enclosure Nominal Depth	11.81 in (300 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 lock 2 cable gland plate bottom 2 door
Door Type	Glass
Mounting Plate Description	Without mounting plate

Complementary

· · · · · · · · · · · · · · · · · · ·	
Body Type	Single piece body
Number Of Doors	Front face 2
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 5 mm double-bar
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body steel Door steel and security glass
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL
Net Weight	103.62 lb(US) (47 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK08 IEC 62262

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480298172
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.39 in (34 cm)
Package 1 Width	40.16 in (102 cm)
Package 1 Length	40.16 in (102 cm)
Package 1 Weight	97.00 lb(US) (44 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	3
Package 2 Height	45.28 in (115 cm)
Package 2 Width	40.16 in (102 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	319.67 lb(US) (145 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations