



Price* : 787.36 USD



Main

Range	Spacial
Product name	Spacial CRNG
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	31.5 in (800 mm)
Enclosure nominal depth	15.75 in (400 mm)
Installation accessory type	Wall-mounting
Device composition	Lock 1 Door 1 Body 1 Cable gland plate 2 bottom
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Body type	Single piece body
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 points lock, 5 mm double-bar
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Steel body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035

Standards	IEC 62208
Product certifications	CUL UL
Product weight	52.7 kg

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480298271
Nbr. of units in pkg.	1
Package weight(Lbs)	115.94
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------