

Product data sheet

Specifications



Climasys Ultra thin resistance heater low starting current 20W 240V 130x250mm

NSYCRS25W240V

Product availability: Stock - Normally stocked in distribution facility

Price*: 244.85 USD

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	25 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable 6.56 ft (2 m)

Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-76...158 °F (-60...70 °C)
Temperature Setting Range	-40...158 °F (-40...70 °C)
Material	silicone rubber
Height	External: 4.33 in (110 mm)
Width	External: 9.06 in (230 mm)
Depth	External : 0.06 in (1.6 mm)
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing Mode	By 4 screws
Mounting Support	Standard mounting plate DIN rail Adhesive Velcro Telequick mounting plate

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480530142
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin	DE
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.5 cm)
Package 1 Width	10.04 in (25.5 cm)
Package 1 Length	11.02 in (28 cm)
Package 1 Weight	10.65 oz (302 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations