

# Product data sheet

## Characteristics

# NSYCRS50W120V

Climasys Ultra thin resistance heater low starting current 50W 120V 200x320mm

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 259.56 USD



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	50 W
Input voltage	120 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

### Complementary

Operating position	Horizontal Vertical
Ambient air temperature for operation	-76...158 °F (-60...70 °C)
Temperature setting range	-40...158 °F (-40...70 °C)
Material	Silicone rubber
Height	External: 7.87 in (200 mm)
Width	External: 12.6 in (320 mm)
Depth	External: 0.06 in (1.6 mm)
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Electrical protection is needed Air sealed enclosure Heaters must be installed with a thermal controller
Fixing mode	By 4 screws
Mounting support	Standard mounting plate DIN rail Adhesive Velcro Telequick mounting plate

### Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
----------	---------------------------------------

Discount Schedule	ES1
GTIN	00785901779308
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9699999999999997
Returnability	N
Country of origin	DE

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------