# **Product data sheet**

Specifications





# ClimaSys standard cooling unit side of enclosure - 2000W at 400 V

NSYCU2K3P4UL

! Discontinued on: Dec 31, 2023

① To be discontinued

Product availability: Stock - Normally stocked in distribution facility

Price\*: 3,345.71 USD

#### Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	460 V AC 60 Hz, 3 phase	
Rated Power	2300 W	
Cooling Power	6820 Btu/h 60 Hz L35-L35 5150 Btu/h 60 Hz L35-L50	

## Complementary

Height	39.33 in (999 mm)	
Width	15.94 in (405 mm)	
Depth	9.33 in (237 mm)	
Line Rated Current	2.5 A	
Inrush Current	10 A	
Power Consumption In W	970 W 60 Hz, L35-L35 1150 W 60 Hz, L35-L50	
Energy Efficiency Ratio	2.1	
Control Type	Electronic controller	
Temperature Setting Range	68113 °F (2045 °C)	
Ambient Air Temperature For Operation	Outside the enclosure 68113 °F (2045 °C) Maximum 113 °F (45 °C) Inside the enclosure 68113 °F (2045 °C)	
Noise Level	65 dB	
Pressure	362.59 psi (25 bar)	
Flow Rate	External circuit 277385.62 Gal/hr(US) (1050 m3/h) 60 Hz Internal circuit 227192.03 Gal/hr(US) (860 m3/h) 60 Hz	
Net Weight	119.05 lb(US) (54 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Cooling Gas Type	R134a 1.30 lb(US) (0.59 kg))	
Type Of Filter	Optional external circuit filter	
Protection Type	Thermal protection T 6 A Short-circuit protection (magnetic)	
Material	Steel	
Color	Grav RAL 7035)	

## **Environment**

Product Certifications	UL
Standards	DIN 3168
Ip Degree Of Protection	IP55 IEC 60529 on the internal circuit) IP34 IEC 60529 on the external circuit)

# Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480653803	
Returnability	No	
Country Of Origin	IT	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.33 in (23.7 cm)
Package 1 Width	15.94 in (40.5 cm)
Package 1 Length	39.33 in (99.9 cm)
Package 1 Weight	119.05 lb(US) (54.0 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	5
Package 2 Height	49.21 in (125.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	753.98 lb(US) (342.0 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information