


Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Range	ClimaSys
Product name	CU
Product or component type	Slim cooling unit block
Mounting type	Door of enclosure
Type of installation	Indoor
Product destination	For enclosure
Mounting mode	By screws
Input voltage	400...460 V 50/60 Hz 460 V 60 Hz
Phase	2 phases
Cooling power	2934 Btu/h 60 Hz L35-L50 3753 Btu/h 60 Hz L35-L35

### Complementary

Height	1696 mm
Width	19.49 in (495 mm)
Depth	7.68 in (195 mm)
Line Rated Current	2.7 A
Inrush current	8.5 A
Power consumption in W	790 W at 60 Hz, L35-L50 660 W at 60 Hz, L35-L35
Energy efficiency ratio	1.7
Control type	Electronic controller
Temperature setting range	68...122 °F (20...50 °C)
Ambient air temperature for operation	50 °C, maximum 20...46 °C, inside the enclosure 20...50 °C, outside the enclosure
Noise level	64 dB conforming to EN/ISO 3746
Pressure	406.11 psi (28 bar)
Flow rate	Internal circuit : 860 m3/h at 60 Hz External circuit : 860 m3/h at 60 Hz
Product weight	114.64 lb(US) (52 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Cooling gas type	R134a (0.5 kg)
Type of filter	Optional external circuit filter
Protection type	Thermal protection : T 4 A Short-circuit protection (magnetic) :
Material	Steel
Colour	Grey RAL 7035

## Environment

Product certifications	UL
IP degree of protection	IP34 on the external circuit conforming to IEC 60529 IP55 on the internal circuit conforming to IEC 60529

## Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	003606480703966
Nbr. of units in pkg.	1
Package weight(Lbs)	114.61
Returnability	N

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------