Product data sheet

Specification





ClimaSys forced vent. IP54, 262m3/h, 24V DC, with outlet grille and filter G2

NSYCVF300M24DPF

Product availability: Stock - Normally stocked in distribution facility

Price*: 205.00 USD

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 69214.32 Gal/hr(US) (262 m3/h)
[Us] Rated Supply Voltage	1230 V
Input Voltage	24 V DC

Complementary

Absorbed Power	13 W
Line Rated Current	0.53 A
Noise Level < At	5556 dB
Bearing Type	Ball
Height	External 10.55 in (268 mm)
Width	External 9.76 in (248 mm)
Depth	External 4.07 in (103.4 mm)
Cut-Out Dimensions	223 x 223 mm
Net Weight	2.43 lb(US) (1.1 kg)
Material	Outlet grille injected thermoplastic (ASA PC)
Color	Outlet grille Gray RAL 7035)
Ambient Air Temperature For Operation	14158 °F (-1070 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Maximum Pressure	158 Pa flow rate 0 m³/h
Connections - Terminals	Cable
Ip Degree Of Protection	IP54
Device Composition	axial motor protective grille on the front and rear surfaces filter front of axial motor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

1 outlet grille front 1 cut-out template 1 power cord Condition Of Use Overfrequent filter replacement should be avoided

Outside temperature must be 5 °C lower than inside temperature Flow rates depends on the work point, see ProClima software Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480151309
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.28 in (18.5 cm)
Package 1 Width	9.84 in (25.0 cm)
Package 1 Length	10.83 in (27.5 cm)
Package 1 Weight	3.00 lb(US) (1.36 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	11.02 in (28.0 cm)
Package 2 Width	16.14 in (41.0 cm)
Package 2 Length	23.23 in (59.0 cm)
Package 2 Weight	14.24 lb(US) (6.46 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	64
Package 3 Height	37.40 in (95.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	222.67 lb(US) (101.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information