

# Product data sheet

Specifications



## Climasys forced vent. 65 m3/hour, 230V, with outlet grille plastic and filter

NSYCVF65M230PF

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 98.33 USD

### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate without filter or grille: 44910.05 Gal/hr(US) (170 m3/h) Free flow rate with standard filter: 17171.49 Gal/hr(US) (65 m3/h) at 50 Hz
Input Voltage	230 V 50/60 Hz

### Complementary

Height	External 4.88 in (124 mm)
Width	External 4.88 in (124 mm)
Depth	External 2.17 in (55 mm)
Cut-Out Dimensions	Ø 108 mm
Material	Outlet grille ABS (acrylonitrile butadiene-styrene) Filter polyurethane foam
Color	Outlet grille Black Filter Black
Ip Degree Of Protection	IP20
Device Composition	1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 outlet grille front

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480151378
Returnability	No
Country Of Origin	FR

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Package 1 Height</b>	2.56 in (6.5 cm)
<b>Package 1 Width</b>	5.91 in (15.0 cm)
<b>Package 1 Length</b>	6.69 in (17.0 cm)
<b>Package 1 Weight</b>	24.44 oz (693.0 g)
<b>Unit Type Of Package 2</b>	CAR
<b>Number Of Units In Package 2</b>	10
<b>Package 2 Height</b>	7.87 in (20.0 cm)
<b>Package 2 Width</b>	15.75 in (40.0 cm)
<b>Package 2 Length</b>	11.81 in (30.0 cm)
<b>Package 2 Weight</b>	16.70 lb(US) (7.576 kg)
<b>Unit Type Of Package 3</b>	PAM
<b>Number Of Units In Package 3</b>	400
<b>Package 3 Height</b>	49.21 in (125.0 cm)
<b>Package 3 Width</b>	39.37 in (100.0 cm)
<b>Package 3 Length</b>	47.24 in (120.0 cm)
<b>Package 3 Weight</b>	674.62 lb(US) (306.0 kg)

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)