



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 212133.96 Gal/hr(US) (803 m ³ /h) at 60 Hz Free flow rate with standard filter: 245948.58 Gal/hr(US) (931 m ³ /h) at 50 Hz
[Us] rated supply voltage	396...466 V
Input voltage	400 V 50/60 Hz

Complementary

Absorbed power	126 W 50 Hz 126 W 60 Hz
[In] rated current	0.226 A 50 Hz 0.232 A 60 Hz
Noise level < at	75...77 dB
Bearing type	Ball
Height	External: 13.23 in (336 mm)
Width	External: 12.44 in (316 mm)
Depth	External: 6.38 in (162 mm)
Cut-out dimensions	291 x 291 mm
Product weight	9.04 lb(US) (4.1 kg)
Material	Injected thermoplastic (ASA PC) outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	5...140 °F (-15...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Maximum pressure	170 Pa flow rate 0 m ³ /h
Connections - terminals	Terminal block
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor

	1 cut-out template
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901698623
Nbr. of units in pkg.	1
Package weight(Lbs)	9.509999999999998
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------