
# Product data sheet

Specifications





# Combined support bracket, PanelSeT SFN, Spacial SF, Spacial SM, steel, set of 10

NSYETF

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 153.78 USD

Μ	a	in	
141	a		

Range	Spacial
Anwendung	Multi-purpose
Product Or Component Type	Support bracket
Mounting Location	On structure of enclosure On mounting plate
Mounting Support	Earthing bar DIN rail
Device Composition	fixing elements 1 combined support brackets
Quantity Per Set	Set of 10

#### Complementary

Material	Zinc coated steel
Height	3.41 in (86.5 mm)
Width	0.79 in (20 mm)
Depth	4.53 in (115 mm)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480064425
Returnability	No
Country Of Origin	US

## **Packing Units**

<b>U</b>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	4.53 in (11.5 cm)
Package 1 Weight	2.36 oz (66.8 g)
Unit Type Of Package 2	BB1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 2	10
Package 2 Height	4.53 in (11.5 cm)
Package 2 Width	5.71 in (14.5 cm)
Package 2 Length	5.91 in (15.0 cm)
Package 2 Weight	26.28 oz (745.0 g)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations